



## DATA SHEET

### 2 WAY METAL MAIN SWITCH CONSUMER UNIT

Catalogue Reference :- NM206/63

Image not to scale

<b>Current Rating</b>	63A
<b>Operating Voltage</b>	240Volts +10/-6%
<b>Short Circuit Rating</b>	16kA when protected by a 100A HRC fuse to BS1361
<b>Insulation Voltage</b>	500Volts AC
<b>IP Rating</b>	IP2XC
<b>Consumer Unit</b>	BSEN 61439-3
<b>Main Switch</b>	BSEN 60947-3
<b>RCD Incomer</b>	BSEN 61008
<b>Colour</b>	RAL 9010
<b>Box Material</b>	Steel
<b>Lid Material (including visor)</b>	Steel
<b>Outgoing Terminal Size Neutral Bar</b>	Maximum cable Size 10mm
<b>Outgoing Terminal Size Earth Bar</b>	Maximum cable size 10mm
<b>Incoming Terminal Size Neutral Bar</b>	Maximum cable size 16mm
<b>Incoming Terminal Size Earth Bar</b>	Maximum cable size 16mm
<b>Incoming Switch Disconnecter Size</b>	Maximum cable size Main Switch 50mm, RCD 35mm



#### Dimensions

<b>Height</b>	185mm
<b>Width</b>	130mm
<b>Box Depth</b>	80mm
<b>Total Depth</b>	104mm

#### Replacement Incoming devices

- **WS602** (main switch)

#### Replacement Spare Items

- **B4471/SPARE** (user operating instructions)
- **NHLABELPACK** (Full Kit of Labels)
- **NM4/MCLA** (complete lid assembly)

<b>Compatible Circuit Protection Devices:</b>			
<b>MCBs</b>		<b>RCBOs</b>	
6kA B curve (3-5In)	6kA C curve (5-10In)	6kA B curve (3-5In)	6kA C curve (5-10In)
NHXB06	NHXC06	NHXSBS1B06	NHXSBS1C06
NHXB10	NHXC10	NHXSBS1B10	NHXSBS1C10
NHXB16	NHXC16	NHXSBS1B16	NHXSBS1C16
NHXB20	NHXC20	NHXSBS1B20	NHXSBS1C20
NHXB32	NHXC32	NHXSBS1B32	NHXSBS1C32
NHXB40	NHXC40	NHXSBS1B40	NHXSBS1C40
NHXB50	NHXC50	NHXSBS1B50	NHXSBS1C50