



Sample photo

**Order symbol:** ABS 200/75 HG  
**Product nbr:** 6081326  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074021779  
**El. number:**  
Finland: 3421701  
Denmark: 8212023372  
Italy: 7361123  
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
<b>mm:</b>	255	180	75	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>	10.0	7.1	3.0	Impact Resistance (EN 62262): IK 07

Materials:		Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
<b>Material:</b>	ABS	
<b>Base colour:</b>	RAL 7035	
<b>Cover colour:</b>	RAL 7035	
<b>Cover screws material:</b>	Polyamide	

Certificates:	
<b>Cover screws colour:</b>	Grey
<b>Gasket material:</b>	TPE
<b>Temperatures:</b>	
<b>Short term:</b>	-40 ... 80 °C
<b>Continuous:</b>	-40 ... 60 °C
<b>Short term:</b>	-40 ... 175 °F
<b>Continuous:</b>	-40 ... 140 °F

Accessories:	
MIV 200	Mounting plate (Galvanized steel)
MIN 15	DIN-15 Mounting rail
MIN 20	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
MIV 20	DIN-35 Mounting rail
FP A 200/180	Front plate (Aluminium)
HFP 180	Front plate hinge series (2 pcs)
FP 22046	Wall fastening lug (4 pcs)

