

FEATURES

- **2.5 m cable length:** Provides ample reach for various setups and installations
- **IEC C19 to CEE 7 connectors:** Ensures compatibility with a wide range of equipment
- **16 A current rating:** Suitable for high-power applications
- **Polyvinyl Chloride jacket:** Offers durability and resistance to wear
- **Black colour:** Blends seamlessly with most environments
- **Straight mains plug and socket:** Facilitates easy and secure connections

RS PRO 16A Power Cable, 2.5 m Length

RS Stock No: 558-952



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO power cable is designed for reliable and efficient power transmission in industrial and commercial settings. With a length of 2.5 metres, it offers flexibility and convenience for connecting devices to power sources. The cable is ideal for applications requiring a 16 A current rating and supports a voltage of up to 250 V.

General Specifications

Connector Type A	IEC C19
Connector Type B	CEE 7
Jacket Colour	Black
Mains Socket Type	Straight
Product Type	Power Cable

Mechanical Specifications

Cable Length	2.5 m
Jacket Material	Polyvinyl Chloride

Electrical Specifications

Current Rating	16 A
Mains Plug Type	Straight
Voltage	250 V

Approvals

Standards/Approvals	CCCs, CEBEC, CSA, D, EAC, ENEC 11, FI, ICC, IMQ, JET, KEMA, KEUR, N, NF, OVE, PSE, R31947, RCM N10544, S, UL, VDA
---------------------	---

