

FEATURES

- **Flush cut type:** Provides precise and clean cuts, reducing the risk of damage to components.
- **High carbon steel jaws:** Offers superior strength and durability for long-lasting performance.
- **Bi-material dolphin handle:** Enhances grip and comfort, reducing hand fatigue during prolonged use.
- **ESD safe:** Protects sensitive electronic components from electrostatic discharge.
- **Overall length of 138 mm:** Compact size for easy handling and access in tight spaces.
- **Maximum cutting capacity of 1.3 mm:** Suitable for a variety of electronic wires and components.

RS PRO Bi-Material Dolphin Handle Flush Cutter, High Carbon Steel Jaws

RS Stock No: 616-311



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO flush cutter is designed for precision cutting in electronic applications. With its high carbon steel jaws and bi-material dolphin handle, it ensures durability and comfort during extended use. Ideal for achieving clean cuts in delicate electronic components, this tool is essential for professionals seeking reliability and precision.

General Specifications

Application	Electronic Applications
Cut Type	Flush
Handle Material	Bi-Material Dolphin
Height Safe	No
Jaw Material	High Carbon Steel
Product Type	Flush Cutter
Sub Type	Flush Cutter

Protection Category

ESD Safe	Yes
Non-Sparking	No
VDE/1000V Approved	No

Mechanical Specifications

Maximum Cutting Capacity	1.3 mm
Overall Length	138 mm

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, IEC 61340-5-1, REACH, RoHS
---------------------	--

