



Figure similar

SIMATIC, terminal module TM-IM/EM60S for ET200iSP, for holding the IM152-1 and an electronic module, screw terminals in black, incl. power bus termination module, Ex eb [ia Ga/ib] IIC T4 Gb, Ex eb [ia IIIC Da] IIC T4 Gb, Ex eb [ia/ib] I Mb

General information	
Product brand name	SIMATIC
Product family	ET 200iSP
Product category	Terminal module
Product type designation	TM-IM/EM60S
Product version	Screw terminals black
Installation type/mounting	
Rack mounting	No
Front mounting	Yes
Rail mounting	Yes
Wall mounting/direct mounting	No
Supply voltage	
Type of supply voltage	DC
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
At DC, max.	4 A
Output voltage	
Type of output voltage	DC
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Output current	
At DC, max.	4 A
Hardware configuration	
Slots	
<ul style="list-style-type: none"> ● Number of slots ● Plug-in modules, analog I/O ● Plug-in modules, digital I/O ● Plug-in modules, function modules and technology modules ● Plug-in modules, communication modules ● Plug-in modules, CPUs ● Plug-in modules, others 	<ul style="list-style-type: none"> 2 Yes Yes No No No Yes
Standards, approvals, certificates	
CE mark	CE 0344
Suitable for safety functions	Yes
reference designation according to IEC 81346-2 (2009)	XX
Use in hazardous areas	

- Explosion protection category for gas No
- Explosion protection category for dust No
- associated equipment (Ex ia) No
- associated equipment (Ex ib) No

Marine approval	
• Germanischer Lloyd (GL)	Yes
• American Bureau of Shipping (ABS)	Yes
• Bureau Veritas (BV)	Yes
• Det Norske Veritas (DNV)	Yes

Dimensions	
Width	60 mm
Height	190 mm
Depth	52 mm

Weights	
Weight, approx.	235 g

Classifications			
		Version	Classification
	eClass	14	27-24-26-03
	eClass	12	27-24-26-03
	eClass	9.1	27-24-26-03
	eClass	9	27-24-26-03
	eClass	8	27-24-26-03
	eClass	7.1	27-24-26-03
	eClass	6	27-24-26-03
	ETIM	10	EC001598
	ETIM	9	EC001598
	ETIM	8	EC001598
	ETIM	7	EC001598
	IDEA	4	3560
	UNSPSC	15	32-15-17-04

Approvals / Certificates

General Product Approval



For use in hazardous locations



For use in hazardous locations | **Maritime application**



Maritime application | **Environment**



last modified:

4/28/2025 