



1-163038-0

TE Part Number: 1-163038-0

 [Active](#)

.200" Centerline, 250 V, 13 A max.



[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Housing
- Contact Diameter = 2.13 mm
- Number of Circuits = 3
- 7.12 mm Centerline, Matrix
- In-Line Contact Layout

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Housing
- Number of Circuits = 3
- Mount = Free or Panel
- Color = Natural
- Lock Type = Positive Lock
- Connector Line = Commercial MATE-N-LOK

Electrical Characteristics:

- Voltage (VAC) = 250

Body Related Features:

- Contact Diameter (mm [in]) = 2.13 [0.084]
- Centerline, Matrix (mm [in]) = 7.12 [.280]
- Housing Type = Plug

Contact Related Features:

- Contact Layout = In-Line

Housing Related Features:

- Housing Material = Polyamide
- Housing Flammability Rating = UL 94V-2

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = One Piece Housing

Other:

- Brand = AMP