

Label sheet, DIN A4 - ES-SSMK-GB 96X30 CUS - 0824409

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Label sheet, DIN A4, can be ordered: Sheet, transparent/white, labeled according to customer specifications, Mounting type: Insert, Lettering field: 92 x 26 mm



The figure shows a similar product



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 352802
Weight per Piece (excluding packing)	9.0 g
Custom tariff number	48025890
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	96 mm
Width (a)	30 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	transparent/white
Base element material	PC
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PC
Marking mounting type	Insert

Label sheet, DIN A4 - ES-SSMK-GB 96X30 CUS - 0824409

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410