

Features

- Medium Duty
- Industrial castor
- Rotation Swivel
- Fixing Plate
- Polyurethane
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing
- Flatfree wheel

RS PRO Castor Wheels

RS Stock No.: 0631180



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description








Flatfree wheel with polyurethane tyre, with high resistance thermoplastic material centre. Hub on plain bore. In zinc-chromium plated pressed steel, turning on double rim of balls. Assembled with self-locking nut. Dust cover ring on the balls.

General Specifications

| | |
|----------------------------------|--|
| Rotation | Swivel |
| Weight Class | Medium Duty |
| Load Capacity (Kg) | 70 |
| Load Capacity / 4pcs (Kg) | 280 |
| Tyre Material | Polyurethane |
| Hub Material | Thermoplastic |
| Bracket Material | Pressed Steel |
| Includes Brake | No |
| Features | Corrosion Resistant, Impact Resistant, Shock Absorbing |
| Applications | Industrial castor |

Operation Environment Specifications

| | |
|--|-------------|
| Operating Temperature (Celsius) | -40° to 80° |
|--|-------------|

| | | | | | | |
|---|---|---|---|---|---|---|
|  |  |  |  |  |  |  |
| 260x85 | 200x160 | 150x115 | 14x26 | 85 | 303 | 70 |

Mechanical Specifications

| | |
|-----------------------------|-------------|
| Mounting Type | Single Bolt |
| Wheel Diameter (mm) | 260 |
| Wheel / Tread Width (mm) | 85 |
| Overall Height (mm) | 303 |
| Number of Fixing Holes | 4 |
| Fixing Hole Size (mm) | 14x26 |
| Hub Bearing Type | Plain Bore |
| Thread Size (M) | |
| Stem Height (mm) | |
| Stem Diameter (mm) | |
| Hardness of Wheel (Shore A) | |
| Levelling Extent (mm) | |
| Offset (mm) | 85 |
| Castor Weight (Kg) | 4.275 |

Fixing Centres Specifications

| | |
|----------------------------|----------|
| Fixing Centres (mm) | 2000x160 |
| Fixing Centres Length (mm) | 200 |
| Fixing Centres Width (mm) | 160 |

Fixing Plate Specifications

| | |
|------------------------------|---------|
| Fixing Plate Dimensions (mm) | 150x115 |
| Fixing Plate Length (mm) | 150 |
| Fixing Plate Width (mm) | 115 |