


FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Standard 1:1 D-SUB module, with spring-cage connection and D-SUB pin strip, no. of positions
37

Your advantages

- 9-pos. ... 50-pos.
- Spring-cage connection technology
- In accordance with IEC 60807-2
- 1:1 connection

Commercial data

Item number	2304018
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	*****
Product key	DK2182
Catalog page	Page 308 (IF-2011)
GTIN	4017918943981
Weight per piece (including packing)	172 g
Weight per piece (excluding packing)	0.77 g
Customs tariff number	85369010
Country of origin	DE

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

Technical data

Product properties

Product type	Interface module
Number of positions	37

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 2.5 A
Current (Total current)	≤ 81.4 A

Air clearances and creepage distances

Rated insulation voltage	125 V
Rated surge voltage	1.2 kV (1.2/50 μs)

Connection data

Connection 1 (control level)

Connection in acc. with standard	IEC 60807-2
Connection method	D-SUB pin strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	37
Insertion/withdrawal cycles	> 500
Pitch	2.77 mm

Connection 2 (field level)

Connection method	Spring-cage connection
Stripping length	7 mm
Number of positions	38
Conductor cross section rigid	0.2 mm² ... 4 mm²
Conductor cross section flexible	0.2 mm² ... 2.5 mm²
	0.25 mm² ... 2.5 mm² (Ferrule without plastic sleeve)
	0.25 mm² ... 1.5 mm² (Ferrule with plastic sleeve)
Conductor cross section AWG	24 ... 12
Pitch	5.08 mm

Signaling

Status display present	No
------------------------	----

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

Dimensions

Item dimensions

Width	101.15 mm
Height	77 mm
Depth	57.47 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP20
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM-D37 SUB/S/ZFKDS - Termination board

2304018

<https://www.phoenixcontact.com/in/products/2304018>



Drawings

Circuit diagram



FLKM-D37 SUB/S/ZFKDS - Termination board





2304018

<https://www.phoenixcontact.com/in/products/2304018>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2304018>

 cUL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	2.5 A	-	-

 UL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	2.5 A	-	-

cULus Recognized				
-------------------------	--	--	--	--

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-12.0	27141152
ECLASS-13.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

Accessories

CABLE D-SUB-S/.../.../... - Cable

2302340

<https://www.phoenixcontact.com/in/products/2302340>



Shielded round cable, assembled with one D-SUB female and pin strip (9-, 15-, 25-, 37-, or 50-pos.), variable cable length

CABLE D-SUB-B-B-S/.../.../... - Cable

2302421

<https://www.phoenixcontact.com/in/products/2302421>



Shielded round cable, assembled with two D-SUB female strips (9-, 15-, 25-, 37-, or 50-pos.), variable cable length

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

CABLE-D37SUB/B/S/ 50/KONFEK/S - Cable

2302191

<https://www.phoenixcontact.com/in/products/2302191>



Assembled shielded round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 0.5 m

CABLE-D37SUB/B/S/100/KONFEK/S - Cable

2302201

<https://www.phoenixcontact.com/in/products/2302201>



Assembled shielded round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 1 m

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

CABLE-D37SUB/B/S/150/KONFEK/S - Cable

2302214

<https://www.phoenixcontact.com/in/products/2302214>



Assembled shielded round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 1.5 m

CABLE-D37SUB/B/S/200/KONFEK/S - Cable

2302227

<https://www.phoenixcontact.com/in/products/2302227>



Assembled shielded round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 2 m

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

CABLE-D37SUB/B/S/300/KONFEK/S - Cable

2302230

<https://www.phoenixcontact.com/in/products/2302230>



Assembled shielded round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 3 m

CABLE-D37SUB/B/S/400/KONFEK/S - Cable

2302243

<https://www.phoenixcontact.com/in/products/2302243>



Assembled shielded round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 4 m

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

CABLE-D37SUB/B/S/600/KONFEK/S - Cable

2302256

<https://www.phoenixcontact.com/in/products/2302256>



Assembled shielded round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 6 m

CABLE-D37SUB/B/S/HF/S/ 1,0M - Cable

1066608

<https://www.phoenixcontact.com/in/products/1066608>



Assembled, shielded, halogen-free round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 1 m

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

CABLE-D37SUB/B/S/HF/S/ 2,0M - Cable

1066609

<https://www.phoenixcontact.com/in/products/1066609>



Assembled, shielded, halogen-free round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 2 m

CABLE-D37SUB/B/S/HF/S/ 3,0M - Cable

1066611

<https://www.phoenixcontact.com/in/products/1066611>



Assembled, shielded, halogen-free round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: 3 m

FLKM-D37 SUB/S/ZFKDS - Termination board

2304018

<https://www.phoenixcontact.com/in/products/2304018>



CABLE-D37SUB-B-S-HF-S/... - Cable

1075562

<https://www.phoenixcontact.com/in/products/1075562>



Assembled, shielded, halogen-free round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB pin strip (1x 37-position); cable length: variable

CABLE-D-37SUB/F/OE/0,25/S/0,5M - Cable

2926221

<https://www.phoenixcontact.com/in/products/2926221>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 0.5 m

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

CABLE-D-37SUB/F/OE/0,25/S/1,0M - Cable

2926234

<https://www.phoenixcontact.com/in/products/2926234>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 1 m

CABLE-D-37SUB/F/OE/0,25/S/1,5M - Cable

2926247

<https://www.phoenixcontact.com/in/products/2926247>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 1.5 m

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

CABLE-D-37SUB/F/OE/0,25/S/2,0M - Cable

2926250

<https://www.phoenixcontact.com/in/products/2926250>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 2 m

CABLE-D-37SUB/F/OE/0,25/S/3,0M - Cable

2926263

<https://www.phoenixcontact.com/in/products/2926263>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 3 m

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

CABLE-D-37SUB/F/OE/0,25/S/4,0M - Cable

2926276

<https://www.phoenixcontact.com/in/products/2926276>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 4 m

CABLE-D-37SUB/F/OE/0,25/S/6,0M - Cable

2926289

<https://www.phoenixcontact.com/in/products/2926289>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 6 m

FLKM-D37 SUB/S/ZFKDS - Termination board



2304018

<https://www.phoenixcontact.com/in/products/2304018>

CABLE-D-37SUB/F/OE/0,25/S/10M - Cable

2906217

<https://www.phoenixcontact.com/in/products/2906217>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 10 m

CABLE-D-37SUB/F/OE/0,25/S/15M - Cable

2906218

<https://www.phoenixcontact.com/in/products/2906218>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 15 m

FLKM-D37 SUB/S/ZFKDS - Termination board

2304018

<https://www.phoenixcontact.com/in/products/2304018>



CABLE-D-37SUB/F/OE/0,25/S/20M - Cable

2906219

<https://www.phoenixcontact.com/in/products/2906219>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: 20 m

CABLE-D-37SUB-F-OE-0,25-S/... - Cable

2900907

<https://www.phoenixcontact.com/in/products/2900907>



Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB socket strip (1x 37-position); cable length: variable

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in