

## SIDEBOARDS AND TROLLEYS



150 KG

### Desks with writing surface

Bare or equipped, fixed or mobile, our desks are real little workstations that can be used for a wide range of purposes: quality control, badging, computer consultation, etc.

- Rectangular tube frame, cross-section 35 × 20 mm
- Equipped with lockable storage space.
- Available in 3 versions: 2 shelves, 4-drawer unit or door unit.
- Set of 2 spanners supplied.
- Choice of 4 glides or 4 swivel castors Ø 50 mm, 2 of which have brakes to EN 1757 standard.

#### Dimensions :

- Shelf: 620 × 470 mm
- 4-drawer unit: 470 × 600 × 620 mm, 2 drawers useful height 100 mm and 2 drawers useful height 150 mm
- Door unit: 470 × 600 × 620 mm, including 1 shelf.



820 005 969



820 008 489



820 005 970

Reference	Models	Feet	Overall dimensions (mm)	Weight kg
820 005 969	2 shelves	Castors	540 x 620 x 1275	24
820 008 487		Skates	540 x 620 x 1205	
820 005 971	1 block of 4 drawers	Castors	540 x 620 x 1275	65
820 008 489		Skates	540 x 620 x 1205	
820 005 970	1 door unit	Castors	540 x 620 x 1275	47
820 008 488		Skates	540 x 620 x 1205	

## OPTIONS



Notice board :  
Supplied with 4 magnetic studs, 520 x 795 mm.  
822 005 973

Sheet metal plate: for hanging plastic document holder options  
822 009 245

Plastic briefcase :  
802 000 001



Partitions for drawers 100 mm high,  
i.e. the first 2 drawers.  
6 partitions included.  
882 006 036



Additional shelf for door unit. 4  
shelves max. with 9 possible  
positions adjustable in 55 mm  
increments.  
882 006 037

## OTHER MODELS AVAILABLE



Models with shelves



Models with reclining top

