

525mm Deep Models

650mm Deep Models

525mm Wide x 525mm Deep

Height (mm)	Shelves	Order Ref.	Price £
600	1	40010095.11V	278.08
700	1	40010096.11V	281.33
800	2	40010097.11V	320.89
900	2	40010125.11V	337.37
1000	2	40010098.11V	353.85
1200	3	40010099.11V	408.80
extra shelf 525 x 525		42101006.51V	25.15

650mm Wide x 650mm Deep

Height (mm)	Shelves	Order Ref.	Price £
800	2	40019120.11V	349.46
900	2	40019163.11V	367.04
1000	2	40019121.11V	384.62
1200	3	40019122.11V	448.36
1600	3	40019158.11V	542.87
2000	4	40019125.11V	615.40
extra shelf 650 x 650		42101011.51V	29.67

800mm Wide x 525mm Deep

Height (mm)	Shelves	Order Ref.	Price £
800	2	40012077.11V	393.42
900	2	40012115.11V	413.20
1000	2	40012078.11V	432.98
1200	3	40012079.11V	500.01
1600	3	40012081.11V	580.23
2000	4	40012084.11V	686.83
extra shelf 800 x 525		42101014.51V	29.01

800mm Wide x 650mm Deep

Height (mm)	Shelves	Order Ref.	Price £
800	2	40020110.11V	418.69
900	2	40020144.11V	439.57
1000	2	40020111.11V	460.45
1200	3	40020112.11V	532.98
1600	3	40020114.11V	616.50
2000	4	40020117.11V	731.89
extra shelf 800 x 650		42101015.51V	33.46

1050mm Wide x 525mm Deep

Height (mm)	Shelves	Order Ref.	Price £
800	2	40013046.11V	442.87
900	2	40013077.11V	457.15
1000	2	40013047.11V	471.44
1200	3	40013048.11V	550.56
1600	3	40013050.11V	613.20
2000	4	40013053.11V	723.09
extra shelf 1050 x 525		42101018.51V	33.46

1050mm Wide x 650mm Deep

Height (mm)	Shelves	Order Ref.	Price £
800	2	40021094.11V	480.23
900	2	40021205.11V	492.61
1000	2	40021095.11V	505.51
1200	3	40021096.11V	589.03
1600	3	40021098.11V	651.66
2000	4	40021101.11V	768.15
extra shelf 1050 x 650		42101019.51V	38.33

1300mm Wide x 525mm Deep

Height (mm)	Shelves	Order Ref.	Price £
800	2	40014046.11V	506.61
900	2	40014066.11V	521.99
1000	2	40014047.11V	537.38
1200	3	40014048.11V	638.48
1600	3	40014050.11V	703.31
2000	4	40014053.11V	822.00
extra shelf 1300 x 525		42101022.51V	47.31

1300mm Wide x 650mm Deep

Height (mm)	Shelves	Order Ref.	Price £
800	2	40022046.11V	540.67
900	2	40022102.11V	556.61
1000	2	40022047.11V	572.54
1200	3	40022048.11V	679.14
1600	3	40022050.11V	743.97
2000	4	40022053.11V	868.15
extra shelf 1300 x 650		42101023.51V	53.08

Housing:

RAL 7035 – light grey

Top, bottom and fronts:

.11 .16 .24 .19

RAL 5010 – gentian blue

RAL 7035 – light grey

RAL 3004 – crimson red

RAL 7016 – anthracite grey

cubio
cabinets

cubio
mobile

cubio
dividers

cubio
cupboards

cubio
benches

perfo

cnc

verso
cabinets

verso
mobile

verso
cupboards

verso
benches

facilities

cases &
seating