

FEATURES

- High pressures and high flow rates
- High quality gaskets
- Class H coils
- Products traceability

RS PRO Pneumatic Solenoid Valves

RS Stock No.: 2554156



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS Pro Solenoid valve has simple and compact design, the fluidity solenoid valves are available in 3/2NC versions. The materials used allow the FLUIDITY solenoid valves to be installed also in food applications or in contact with aggressive fluids and reach working temperatures from -40°C to +180°C. The proposed coils allow to obtain high performances and on request low power consumption.

General Specifications

Materials

Body/Sub-Base	Brass
----------------------	-------

Electrical Specifications

Supply Voltage	24 V
-----------------------	------

Mechanical Specifications

Number of Ports	3/2 NC
Connection	1/4 G female
Connection Size	1/4 in
Operation	Solenoid

Operation Environment Specifications

Operating Temperature Range	-10°C to +80°C
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	40°C

Approvals

Standards Met	EN1127, EN80079-36, EN80079-37
Declarations	EU Declaration of Conformity, UE Declaration of Conformity

**CONSTRUCTIONAL/SCHEMATIC DIAGRAMS /ACCESSORIES
WITH PRODUCT**