

VARTA Indestructible BL20 Pro with 6AA Batt.



Extremely robust (4m drop test, IP54) LED Beam Lantern with two light levels impact resistance IK08 and shock absorbing rubber head.



Information

- Extremely robust beam lantern (4m drop test) with shock-absorbing rubber elements
- Impact resistant lens and reflector
- impact resistance rating IK08 (IEC 62262)
- 4m drop test
- Splash-water and dust protected (IP54)
- Bright high performance LED
- 2 light levels: high and low
- Designed for maximum durability
- Operated with 6AA batteries (incl)

Article Details

Ordernumber	18751 101 421
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	(up to) 400.00 m
Runtime	(up to) 85 h
Total light output	(up to) 400 lm
Equipped with	6 x AA Longlife Power
Product Diameter mm	84.00
Product Length / Depth mm	150.00
Product Width mm	84.00
Product Height mm	125.00
Product Weight g	520.00

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 987115	180.00	96.00	240.00	0.73
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	2	40 08496 987122	248.00	184.00	194.00	1.60
PAL (Pallet)	190	40 08496 987139	800.00	1,200.00	1,120.00	173.44
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
5	19		95		2	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.
VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

