



STANLEY® FATMAX™ 230mm PRO Box Torpedo Level



XTHT0-42495 - STANLEY® FATMAX™ 230mm PRO Box Torpedo Level

STANLEY FATMAX® box beam levels have been designed to provide durability and accuracy, providing you with the performance you need for every job. The patented continuous edge enables the ability to draw or scribe uninterrupted lines along the full length of the level. The fine milled primary edge provides 0.5mm/m accuracy.

- Box torpedo spirit level with two fixed vials and a 360° rotating vial for flexible measuring
- Extra large centre vial for easier reading and increased accuracy
- Magnetic base for easier work on steel structures and scaffolding
- No-Mar rubber end caps for greater shock resistance
- Extruded aluminium housing for increased rigidity and reduced weight
- Accuracy: 0.5mm/m

Length (mm): 230 mm

Number of Vials: 3

Accuracy: 0,5 mm/m

Magnetic: Yes

Material: Aluminium

If your STANLEY product becomes defective due to faulty materials or workmanship within 12 months from the date of purchase, STANLEY guarantees to replace all defective parts free of charge or – at our discretion – replace the unit free of charge. See <https://www.2helpu.com/STANLEY> for more information.