

## FEATURES

- **Encapsulated design:** Provides robust protection against dust and moisture, ensuring durability in harsh conditions
- **Constant voltage operation:** Delivers consistent power output, enhancing the reliability of LED systems
- **Wide input voltage range (176-264 V AC):** Offers flexibility and compatibility with various power sources
- **High output power of 350W:** Supports demanding LED applications with ease
- **IP67 rating:** Ensures complete protection against dust and immersion in water, suitable for outdoor use
- **Single output:** Simplifies installation and reduces wiring complexity
- **Wire terminal type:** Facilitates easy and secure connections

## RS PRO 350W Encapsulated LED Driver, 48V Output

RS Stock No: 122-235



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

### Product Description

The RS PRO 350W Encapsulated LED Driver is designed to provide reliable power conversion for LED lighting systems. With a constant voltage output of 48V, it ensures stable performance for high-demand applications. Its encapsulated design offers enhanced protection, making it ideal for use in challenging environments.

### General Specifications

Configuration	Encapsulated
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC to DC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver
Terminal Type	Wire

### Electrical Specifications

Driver Current	7.2 A
Input Voltage	176-264 V ac
Input Voltage Type	AC
Maximum Output Power	350 W
Output Voltage	48 V

### Protection Category

IP Rating	IP67
-----------	------

### Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, CE, EN55015, EN61000-3-2, EN61000-3-3, EN61327-1, EN61347-2-13, EN61547, UKCA
---------------------	---

