

Datasheet

RS Pro Stainless Steel Extension Spring

Stock No: 821-504



Product Details

Stainless Steel Extension Springs

Material to DIN 17224 No. 1 4310 or BS2056 EN58A with a right hand helix

All dimensions conform to DIN 2097 (Grade 2)

Specifications

Material	Stainless Steel
Free Length	35mm
Maximum Extended Length	101.50mm
Outside Diameter	7mm
Wire Diameter	0.63mm
Initial Tension	1N
Spring Rate	0.13N/mm