

# ACTIVARMR®

PERSONAL PROTECTIVE GEAR

## 42-474

Flexible full-length heat barrier.

Previously known as: Crusader Flex 42474



Heat



Heavy Duty

## Heat-resistant full-length gloves, offering complete protection and added comfort

- **Specialized protection:** ActivArm<sup>®</sup> 42-474 industrial gloves possess a full-length heat barrier and can confidently handle dry, hot objects up to 250°C/480°F
- **Elevated comfort:** These heat-resistant gloves' two-piece construction features no outseams, enhancing finger comfort and flexibility, while a sweat-absorbent nonwoven felt liner limits perspiration
- **Assured durability:** Their bonded nitrile coating grants them additional snag, puncture, cut and abrasion resistance
- **Enhanced grip:** ActivArm<sup>®</sup> 42-474 heat-resistant work gloves also provide excellent grip in dry or oily conditions
- **Reduced health risks:** These heavy-duty gloves contain no asbestos, eliminating all related health risks



### Industries

- Automotive
- Chemical
- Food Processing

### Applications

- Press injection molding
- Handling molded structural parts
- Testing
- Welding

# ACTIVARMR®

PERSONAL PROTECTIVE GEAR

## 42-474

Flexible full-length heat barrier.

Previously known as: Crusader Flex 42474

### Key Features

- **Felt insulation and heat barrier:** Hot and dry handling (250°C/480°F)
- **Outseam-free two-piece construction:** Enhanced comfort and flexibility
- **Bonded nitrile coating:** Snag, puncture, abrasion and cut resistance

### Performance Standards & Regulatory Compliance

REACH Compliant



0493



CUT



2241B



X2XXXX

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm <sup>®</sup> 42-474	<b>Liner Material:</b> Non-Woven Polyester, Polycotton <b>Cuff Style:</b> Gauntlet	N/A	8, 9, 10	343-356 mm; 13.5-14 inches	• 12 Pair Per Bag; 6 Bags Per Carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.