

370032091

Stainless steel industrial enclosure IGSN A2 350 x 250 x 97 mm

Stainless steel industrial enclosure IGSN A2 350 x 250 x 97 mm

Drawing 3D Data

Technical data

Height	350 mm
Width	250 mm
Depth	97 mm
Material	Stainless Steel
Material quality	1.4301/304
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-60 °C
temperature max.	175 °C
Seal material	VMQ-(silicone)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV
Approvals	LR (Lloyd's Register), UL (508A)

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tarif number	85369095
Weight	3.69 kg
GTIN	4057624608545

ETIM classification

ETIM 8	EC000058

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



100110670
Mounting plate for 37.003209




100614250
DIN rail 35/7,5 for xx.163609



100620030
Earth rail for 01.163609



371050000
Stainless steel external mounting brackets



379900010
Mounting set for Stainless-steel enclosures