vacuum suction cup ESV-40-BS Part number: 191062

Wearing part, easily replaceable



Data sheet

Feature	Value
Suction cup height compensator	9.5 mm
Min. workpiece radius	90 mm
suction cup diameter	40 mm
suction cup volume	11.699 cm3
Position of connection	on top
Assembly position	Any
Suction cup shape	Round, bellows 1.5 conv
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Food-safe	See Supplementary material information
Ambient temperature	-30 180 °C
Retention force at nominal operating pressure	52.3 N
Product weight	9.8 g
Colour	transparent
Shore hardness	50 +/- 5
Materials note	Free of copper and PTFE
	Contains PWIS substances
	Conforms to RoHS
Material suction cup	VMQ (silicon)

FESTO

