

Features

- Clear
- Instant heat
- R7s round caps
- 230V voltage
- 10 x 118mm
- 8000h life

RS PRO 300W Infrared Heat Lamp

RS Stock No.: 796-0303



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A clear infrared lamp used for applications that require instant shortwave drying. Constructed from quartz the lamps convert virtually all the energy supplied into heat with minimal wastage. The infrared heat lamps can be temperature controlled using a power regulator.

General Specifications

Lamp Type	Infrared
Lamp Base	R7S
Lens Colour	Clear
Life hours	8000h
Applications	Shortwave Drying

Electrical Specifications

Voltage Rating	230V
Wattage	300W

Mechanical Specifications

Diameter	10mm
Length	118mm

Similar Products

Length (mm)	Wattage (W)	Voltage (V)	End Style	Stock No
118	100	230	R7S (Push in)	796-0328
118	150	230	R7S (Push in)	796-0296
118	200	230	R7S (Push in)	796-0293
118	300	230	R7S (Push in)	796-0303
118	500	230	R7S (Push in)	796-0312
216	500	230	SK15 (Wired)	796-0331
216	500	230	SK15 (Wired)	796-0372
350	1000	230	SK15 (Wired)	796-0338
254	500	230	R7S Push in	796-0375
210	500	230	X-STRAP	796-0362
370	1000	230	X-STRAP	796-0353
370	1000	230	X-STRAP	796-0350