

KERN KDP 3000-2



Universal weighing platforms for flexible connection in process chains



Dimensions weighing platform (W×D×H) 165×165×73 mm

Material weighing plate stainless steel

Material platform Plastics

Material display housing No display available

Level indicator ✓

Levelling feet adjustable ✓

Cable length 1,2 m

Display device cable length 1,5 m

Functions

IP protection - display no IP protection

Auto-off interval(s) in mains power mode off

Interface

Interfaces Ethernet (optional, factory)
WiFi (optional, factory)
Bluetooth BLE (v4.0) (optional, factory)
USB-Device

compatible with EasyTouch ✓

Power Supply

Supplied power supply Power supply unit

Plug-in power supply type USB including power supply

Plug-in power supply / adapter for countries - included with the delivery EURO
UK
US
CH

Input voltage power supply / power [Max] 100 V - 240 V, 50 / 60 Hz

Input voltage device / power [Max] 5 V, 1 A

Environmental conditions

Ambient temperature [Min] 5 °C

Ambient temperature [Max] 35 °C

Humidity of environment [Max] 80 %

Approval

CE mark ✓

Services (optional)

Article number for DAkkS calibration 963-127

Article number for certificate of conformity 969-517

Category

Brand KERN
Product category Component
Product group Digital platform
Product family KDP

Measuring System

Weighing system Strain gauge
Weighing capacity [Max] 3,5 kg
Readability [d] 10 mg
Reproducibility 20 mg
Linearity ± 50 mg
Resolution 350.000
Adjustment options Adjusting with external weight
Recommended adjusting weight 3 kg (F1)
Stabilization time 3 s
Warm-up time 120 min
Eccentric loading at 1/3 [Max] 50 mg
Maximum creep (15 minutes) 100 mg
Maximum creep (30 minutes) 200 mg
Default unit g

Construction

Dimension housing (W×D×H) 165×166×75 mm
Dimensions completely mounted (W×D×H) 165×166×75 mm
Dimension display device (W×D×H) 0×0×0 mm
Dimensions weighing surface (W×D) 160×160 mm
Dimensions weighing surface 160×160 mm

KERN KDP 3000-2



Universal weighing platforms for flexible connection in process chains

Packing & Shipping

| | |
|------------------------------|----------------|
| Delivery time | 1 d |
| Dimensions packaging (W×D×H) | 250×355×160 mm |
| Shipping method | Parcel service |
| Net weight approx. | 1,6 kg |
| Gross weight approx. | 2,2 kg |
| Shipping weight | 2,8 kg |

Pictograms

STANDARD



OPTION



FACTORY

