



## 413.3267-7

# FLUSH-MOUNTING SOCKET

32A 6P+E 6h 380-415V 50Hz 60Hz 75X75MM  
Screw terminals

Product Approvals

TECHDATA		STANDARDS AND LAWS	
Commercial series	OPTIMA-SEVEN Series	EN 60309-1 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Type of product	FLUSH-MOUNTING SOCKET	EN 60309-1/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Synthetical description	FLUSH-MOUNTING SOCKET	EN 60309-1/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Rated current	32A	DIRECTIVE LOW VOLTAGE 2014/35 /UE	[European Directives] Low Voltage Directive
Poles	6P+E		
Hour position	6h		
Rated voltage (range)	250-400V		
Rated voltage	380-415V		
Working frequency	60Hz		
Working frequency	50Hz		
Colour	RED		
Material	THERMOPLASTIC		
Protection degree	Splash proof		
Protection degree IP	IP44		
Types of available outlets	ANGLED		
Terminals	Screw terminals		
Flange	75X75MM		