

Features

- 5 mm pitch
- Voltage Rating: 300V
- Current Rating: 10A
- Low Mating Force
- Low Profile
- 5 WAY PCB Terminal Block with Screw Down Termination

RS PRO 5mm Pitch PCB Terminal Block with Screw Down Termination, 5 Way

RS Stock No.: 0631131



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- RS Pro 5-way PCB terminal block with screw down termination, features beryllium copper spring contacts and receptacles to mate with PCB header strip on a 5 mm pitch. .
- These stackable PCB mounting terminals are rated at 10A/300V.
- Standard accepts wire 28-16AWG 1.5 mm²

General Specifications

Number of Contacts	5
Number of Rows	1
Pitch	5mm
Mounting Type	Through Hole
Type	Plug
Body Orientation	Straight
Number of P	5
Termination Method	Screw (M2.6, Steel(A3), Zinc Plated
Torque	0.4N.m
Clamp	Phosphor Bronze
Wire Cage	Brass, Nickel plated
Housing	PBT(UL94V-0)
Colour	Dark grey

Electrical Specifications

Voltage Rating	300V
Current Rating	10A
Insulation Resistance	500M ohm min
Withstanding Voltage	1500V AC/minute

Mechanical Specifications

Mounting Type	Through Hole
Pitch	5.0 mm
Width	10.9mm
Depth	13.3mm

Operation Environment Specifications

Operating Temperature	-40°C to 105°C
-----------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, UL, CE
Declarations	Reach

Spec Drawings

