






MARKING:



MARKING:



1373355	L=500±30
1373356	L=1000±50
1373357	L=1500±50
1373358	L=2500±50



1373355	L1=100±30
1373356	L1=150±30
1373357	L1=180±30
1373358	L1=200±30

WIRING COLOR:

E: Yellow/Green
N: Blue
L: Brown

LENGED ON CORD: (E06-14)

NF-USE 1346 IEMMEQU H05VV-F 3G 1.5mm² 300/500V -LF-

No	BOM ITEM	Q' TY	P/N
1	97606-1 TERMINAL	2 pcs	BBN97606
2	97607-1 TERMINAL	1 pcs	BBN97607
3	IS-018 INNER BODY(BLACK)	1 pcs	MP020S12
4	PVC 45P (SA87, IS-018)	30 g	RPP04512
5	98739PS-0 BLADE	3 pcs	BBP98739
6	IS-16 INNER BODY(BLACK)	1 set	MI016S12
7	PVC 45P (SA87, IS-16B)	30 g	RPP04512
8	PE TIE (BLACK, 8 inch)	1 pcs	KBB10008
9	PE BAG(120*290)	1 pcs	KPR11000
10	LABEL(45*25)	1 pcs	

NOTE:1. CORD 128
2. CONTENT 137335X



CABLE	H05VV-F 3G 1.5 DENT PRINT CT-12(BLACK)				
PLUG	IS-018 + IS-16B	LENGTH	L	UNIT	mm
CLIENT	NAME	First connectivity	N/W	UNIT	kg
	P/N	137335X	SG DWG	SR-172524-9	VER. A

Design. by	楊東	17.07.17
Review. by	楊望春	17.07.17
Approval. by	朱曉玲	17.07.17

X8B JE3016 12 XXX 01