

FEATURES

- High temperature and curve able
- Insulated hot junction for reduced electrical interference
- Mineral insulation for flexibility
- Durability and high performance
- Simple push-in process via probe glands and flange
- M20 cable gland
- 6mm diameter probe

RS PRO Type K Thermocouple 200mm Length, 6mm Diameter → +700°C

RS Stock No.: 621-2401



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS Pro a range of type J and Type K thermocouple temperature sensors or probes that conform to IEC 584 standards. These thermocouple temperature probes have a durable construction and feature a 310 stainless steel mineral insulated flexible sheath that can be bent and formed to suit a wide range of applications. The thermocouple has an insulated hot junction for a reduction in electrical interference. One end of the thermocouple is terminated with a compact KNE terminal head the gives protection to the connections

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-40 to 1000°C
Construction	Stainless steel 310 probe sheath for resistance to corrosion and oxidation
Measuring Junction	Underground
Response Time	5s
Application	Heat exchangers, power stations, brick and cement kilns, heat treatment and annealing furnaces, thermostats, food thermometers, vehicle diagnostics and in laboratories

Mechanical Specifications

Probe Diameter	6mm
Probe Length	200mm
Probe Body Material	310 Stainless Steel
Termination Type	Connection Head

Protection Category

IP Rating	IP67



Approvals

Standards Met	RoHS Compliant
Compliance/Certifications	IEC 584



Other dimensions:

Length Diameter	200 mm	400 mm	600 mm	
6 mm	621-2401	621-2423	621-2445	



		T/C Type	Conductors	Lengtl	h	Termination	+Positive tail wire	-Negative tail wire code	Allied Code	RS order Code
		'K'	1/0.2mm	1 met	re	Mini plug	Green	White	70643600	363-0250
		'K'	1/0.2mm	2 met	re	Mini plug	Green	White		110-4482
		'K'	1/0.2mm	5 met	re	Mini plug	Green	White		123-6306
		'K'	1/0.2mm	10 me	tre	Mini plug	Green	White		123-6307
		'n	1/0.2mm	1 met	re	Mini plug	Black	White	70643599	363-0244
		J'	1/0.2mm	2 met	re	Mini plug	Black	White		123-6308
		'J'	1/0.2mm	5 met	re	Mini plug	Black	White		123-6309
T/C Type	Cı	'J'	1/0.2mm	10 me	tre	Mini plug	Black	White		123-6310
'K'	1/	'T'	1/0.2mm	1 met	re	Mini plug	Brown	White	70643601	363-0266
'K'	1/	'T'	1/0.2mm	2 met	re	Mini plug	Brown	White		123-6311
'K'	1/	'T'	1/0.2mm	5 met		Mini plug	Brown	White		123-6312
'K'	1/	'T'	1/0.2mm	10 me	tre	Mini plug	Brown	White		123-6313
'n	1/0	.2mm	1 metre	М	ini plug	Black	White	70643599	363-0244	ode
T'	1/0	.2mm	2 metre	M	ini plug	Black	White		123-6308	oue
'J'	1/0	.2mm	5 metre	M	ini plug	Black	White		123-6309	
J'	1/0	.2mm	10 metre	М	ini plug	Black	White		123-6310	
'T'	1/0	.2mm	1 metre	М	ini plug	Brown	White	70643601	363-0266	
'T'		.2mm	2 metre		ini plug	Brown	White		123-6311	
'T'		.2mm	5 metre		ini plug	Brown	White		123-6312	
'T'	1/0	.2mm	10 metre	М	ini plug	Brown	White		123-6313	
	K		1/0.31			n/-White	50 metres	70657205	827-6019	
	Т		1/0.31	5mm	+Brow	/n/-White	25 metres	70657208	827-6028	3
	Т		1/0.31	mm	+Brow	n/-White	50 metres	70657206	827-6022	2
	J		1/0.50	3mm	+Black	c/-White	25 metres	70657197	827-5990)
	J		1/0.50	3mm	+Black	c/-White	50 metres	70657201	827-6003	3
	K		1/0.50	3mm	+Gree	n/-White	25 metres	70657203	827-6012	2
	K		1/0.50	3mm	+Gree	n/-White	50 metres	70657204	827-6016	5
	J		7/0.2m	m	+Black	x/-White	25 metres	70657202	827-6006	5
	K		7/0.2m	m	+Gree	n/-White	25 metres	70657207	827-6025	5
	Т		7/0.2m	m	+Brow	n/-White	25 metres	70657209	827-6031	ι
	Ν		7/0.2m	m	+Pink	/-White	25 metres	70657210	827-6034	1



	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Exten	sion:					
KX	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
KX	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
KX	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
KX	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
JX	7/0.2mm	+Black/-White	Black	10 metres	70641640	219-4753
JX	7/0.2mm	+Black/-White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-White	Black	50 metres	70657078	827-5596
JX	7/0.2mm	+Black/-White	Black	100 metres	70637079	236-3915
JX	7/0.2mm	+Black/-White	Black	200 metres	70657081	827-5606
JA	7/0.211111	+blacky-willte	DIdCK	200 metres	70037061	827-3000
TX	7/0.2mm	+Brown/-White	Brown	10 metres	70641637	219-4703
TX	7/0.2mm	+Brown/-White	Brown	25 metres	70641734	236-3870
TX	7/0.2mm	+Brown/-White	Brown	50 metres	70657095	827-5653
TX	7/0.2mm	+Brown/-White	Brown	100 metres	70651749	762-1146
TX	7/0.2mm	+Brown/-White	Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Compensating:						
VX (KCB)	7/0.2mm	+Green/-White	Green	10 metres	70657082	827-5609
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	70641629	219-4551
VX (KCB)	7/0.2mm	+Green/-White	Green	50 metres	70657080	827-5603
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	70641630	219-4573
VX (KCB)	7/0.2mm	+Green/-White	Green	200 metres	70657083	827-5612
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	70657086	827-5621
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	70657087	827-5625
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	70657090	827-5634
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	70651750	762-1152
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	70657096	827-5656
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	70646158	611-7902
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	70657097	827-5659
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	70641641	219-4769
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	70657093	827-5643
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	70657094	827-5647



T/C Type	Conductors	Cores	Reel Length	Allied code	RS order code
KX	1/0.2mm	+Yellow/-Red	25 metres	70656106	814-0030
KX	1/0.2mm	+Yellow/-Red	50 metres	70656111	814-0049
KX	1/0.2mm	+Yellow/-Red	100 metres	70656109	814-0042
KX	7/0.2mm	+Yellow/-Red	25 metres	70656110	814-0046
KX	7/0.2mm	+Yellow/-Red	50 metres	70656113	814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
TX	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
TX	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
TX	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
TX	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
TX	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
TX	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109

T/C Type	Conductors	Cores	Jacket	Reel Length	Allied code	RS order code		
Extension:								
KX	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656102	814-0018		
KX	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656105	814-0027		
KX	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656103	814-0020		
JX	7/0.2mm	+ White/-Red	Black	25 m	70656096	813-9995		
JX	7/0.2mm	+ White/-Red	Black	100 m	70656098	814-0005		
JX	7/0.2mm	+ White/-Red	Black	200 m	70656099	814-0008		
TX	7/0.2mm	+Blue/-Red	Blue	25 m	70656119	814-0074		
TX	7/0.2mm	+Blue/-Red	Blue	100 m	70656122	814-0083		
TX	7/0.2mm	+Blue/-Red	Blue	200 m	70656123	814-0086		
Compensating:								
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656127	814-0103		
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656130	814-0112		
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656131	814-0115		
in (neb)	7/01211111	renow, nea		200	,0050151	01.0110		