



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (1% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2834385-2
RELEASE POKE-IN
CONNECTOR_2P_NATURAL



TE Part # 2305908-3
SMT TB R/A HEADER, 5.0MM, 3 POS




TE Part # 2834167-3
RELEASABLE SLIM CONTACT



TE Part # 2834334-2
4.0PITCH ITB CONN_2P_W
CAP_NATURAL


Customers Also Bought




TE Part #3-2176605-9
RLC73PW 3A R14 1% 2K RL



TE Part #8-1415006-1
RTH14012



TE Part #641294-1
MR RECPT 26-18 PTPHBZ



TE Part #735278
EPEZT * STECKHUELSE ISOLIERT 6,3
X 1,0*



TE Part #1419108-7
RT28516



TE Part #1393240-6
RT314615



TE Part #520971-1
ULTRA-POD 250 ASY REC 18-14 AWG
BR



TE Part #350967-1
MR PIN PTPPHBZ



TE Part #ANT-450-HSW-TNC
Antenna HSW 450 IP67 TNC Jack



TE Part #2388502-1
CHARGE INLET, COMBO 2, LED, 90
DEGREE

Documents

- Product Drawings
- SMT TB PERP PLUG, RET, 5.0MM, 3 POS
- English
- CAD Files
- 3D PDF
- 3D



Customer View Model

[ENG_CVM_CVM_2213935-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213935-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213935-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Buchanan WireMate SMT](#)

English

[BUCHANAN WireMate Connectors Brochure](#)

[BUCHANAN WireMate Connectors Brochure](#)

English

Agency Approvals

[CSA Certificate](#)

English