

HC-B 16-APV-GY - Cover plate



1661121

<https://www.phoenixcontact.com/in/products/1661121>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

HEAVYCON cover plate, for wall cutouts of type B16, 7 mm thick, gray



Commercial data

Item number	1661121
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF7
Product key	AF7AZD
Catalog page	Page 664 (C-2-2019)
GTIN	4017918022471
Weight per piece (including packing)	30.47 g
Weight per piece (excluding packing)	29.91 g
Customs tariff number	39269097
Country of origin	DE

HC-B 16-APV-GY - Cover plate



1661121

<https://www.phoenixcontact.com/in/products/1661121>

Technical data


Notes

General	For wall cutouts of type B16
---------	------------------------------

Product properties

Product type	Cover plate
Type	B16
Seal present	yes

Dimensions

Dimensional drawing	
Width	52 mm
Height	52 mm
Length	123 mm
Drill hole distance, horizontal	103 mm
Drill hole distance, vertical	32 mm
Hole diameter	4.5 mm

Installation dimensions

Width of the assembly cutout	36 mm
Length of the assembly cutout	86 mm

Material specifications

Material	PA
Flammability rating according to UL 94	HB

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 100 °C


HC-B 16-APV-GY - Cover plate



1661121

<https://www.phoenixcontact.com/in/products/1661121>

Drawings



Processing area 2 mm thick

HC-B 16-APV-GY - Cover plate



1661121

<https://www.phoenixcontact.com/in/products/1661121>

Classifications

ECLASS

ECLASS-11.0	27440201
ECLASS-12.0	27440201
ECLASS-13.0	27440201

ETIM

ETIM 9.0	EC002309
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-B 16-APV-GY - Cover plate



1661121
<https://www.phoenixcontact.com/in/products/1661121>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in