

Features

- 75Ω impedance
- 4GHz frequency
- Suitable for RG59 cable
- Nickel plated body
- Copper contacts
- Cable mount

RS PRO BNC Coaxial Connector Plug

RS Stock No.: 546-4869



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A BNC coaxial connector with a Nickel plated body designed for use with coaxial cable and featuring an easy-to-terminate cable crimp design. BNC RF connectors are commonly found in radio and television broadcast equipment.

General Specifications

Coaxial Connector Type	BNC Connector
Gender	Male
Mounting Type	Cable Mount
Termination Method	Crimp
Body Orientation	Straight
Cable Type	RG59
Bulkhead	No
Body Material	Brass
Body Plating	Nickel
Contact Material	Copper
Contact Plating	Gold
Application	Television and radio broadcast
Insulation Material	PTFE
Number Of Functions	500

Electrical Specifications

Impedance	75Ω
Polarity	Normal
Operating Frequency	4GHz
Voltage Rating	500V

Operation Environment Specifications

Minimum Operating Temperature	-20°C
Maximum Operating Temperature	80°C