


## FEATURES

- **Leading Edge, PWM, Trailing Edge Dimming Operation:** Offers versatile dimming options for customised lighting control
- **8.3 A Driver Current:** Provides ample current for high-power LED applications
- **200-240 V AC Input Voltage:** Compatible with standard AC power supplies
- **IP66 Rating:** Ensures protection against dust and powerful water jets, ideal for challenging environments
- **Constant Voltage Operation:** Maintains consistent voltage output for reliable LED performance
- **Single Output:** Simplifies installation and reduces wiring complexity

## RS PRO 200W LED Driver, 24V Constant Voltage

RS Stock No: 642-791



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO 200W LED Driver is designed to provide reliable and efficient power to LED lighting systems. With a constant voltage output of 24V, it ensures stable performance for various lighting applications. Its robust construction and IP66 rating make it suitable for both indoor and outdoor use, offering protection against dust and water ingress.

### General Specifications

Dimming Operation	Leading Edge, PWM, Trailing Edge
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

### Electrical Specifications

Driver Current	8.3 A
Input Voltage	200-240 V ac
Input Voltage Type	AC
Maximum Output Power	200 W
Output Voltage	24 V

### Protection Category

IP Rating	IP66
-----------	------

### Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, 3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547
---------------------	---