



Dry-Shrink™ HSTT100-48-5-3 Heat Shrink

HSTT100-48-5-3

Thin wall heat shrink, 1" (25.4mm) diameter, orange cross-linked polyolefin, 5 pc. package quantity.

Specifications

Product Type	Heat Shrink Tubing
Adhesive Lined	No
Color	Orange
Material	Cross-Linked Polyolefin
Maximum Operating Temperature (°C)	135
Maximum Operating Temperature (°F)	275
Minimum Operating Temperature (°C)	-55
Minimum Operating Temperature (°F)	-67
Nominal Diameter (In.)	1
Nominal Diameter (mm)	25.4
Nominal Recovered Wall Thickness (In.)	0.035
Nominal Recovered Wall Thickness (mm)	0.9
Sub Brand	Dry-Shrink™
Overall Length (In.)	48
Overall Length (ft.)	4
Overall Length (m)	1.22
Overall Length (mm)	1219
Resistance Properties	Flame-Retardant
Standards Met	UL Recognized, CSA Approved, MIL SPEC
Shrink Ratio	2:1
Shrink Temperature (°C)	90
Shrink Temperature (°F)	194
Maximum Recovered Inside Diameter (In.)	0.5
Maximum Recovered Inside Diameter (mm)	12.7
Minimum Expanded Inside Diameter (In.)	1
Minimum Expanded Inside Diameter (mm)	25.4
Application	For Dry Locations

Packaging Detail

UPC	07498362277
Std. Pkg. Qty.	5
Std. Pkg. Volume (cf)	0.3474
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000