

Product data sheet

Specifications



Repacked, Multifix Air, apparatus box, 2 gangs, 67x40 mm

IMT35000W



This repacked option saves 9.31 over the standard condition

Main

Range of product	Multifix
Product name	Multifix Air
Product or component type	Apparatus box
Device application	For airtight installation

Complementary

Function available	Anti-rotation system
Number of gangs	2 gangs
fixing mode	By supplied screw
Material	PP/TPE
Mechanical robustness	Airtight Fire resistance
Colour tint	Green (NCS S 2070-G80Y)
Cable entry	4 knock-outs
Distance between centers	71 mm
drill diameter/depth	67 mm 40 mm
Distance between supports	60 mm
Height	71 mm
Width	142 mm
Depth	39 mm

Environment

Ambient air temperature for operation	-5...60 °C
IP degree of protection	IP40
fire resistance	850 °C
Standards	EN 60670-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	7.000 cm
Package 1 Length	14.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	62.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	40
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.956 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

9 kg CO2 eq.

Use Better



Materials and Substances

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No