

Main

Range	Odace
Product or component type	Blind cover
Device presentation	Mechanism with fixing frame
Type of packing	Paint cover



Complementary



Device mounting	Flush
Fixing mode	By screws
Colour tint	Aluminium
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame
Height	71 mm
Width	71 mm
Depth	27.7 mm
Embedding depth	11.7 mm
Net weight	0.02 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	EN 60669-1 2006/95/EEC
Product certifications	LCIE: NF 619318A[RETURN]JNF
IK degree of protection	IK04
IP degree of protection	IP21D

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	31