

Previously known as: VULCAIN 2100 M V18



Heat



Heavy Duty

Cotton terry loop gloves, granting superior thermal insulation

- **Increased defenses:** ActivArm[™] 97-335 thermal work gloves' cotton terry outer layer provides flexible heat resistance that does not hold on to heat, which results in excellent insulation and hand protection, allowing for intermittent contact with hot parts and materials up to 250°C
- **Improved protection and durability:** These safety gloves possess a polycotton jersey inner layer that grants added heat protection and comfort while protecting hands from abrasion and cuts
- **Added features:** Owing to their extended cuff, ActivArm[™] 97-335 mechanical protection gloves ensure optimal forearm protection



Industries

- Automotive
- Glass manufacturing
- Transportation

Applications

- Rough casting and cores
- Welding
- Press work
- Stamping press shop
- Handling hot metal castings
- Glass repair and replacement

Previously known as: VULCAIN 2100 M V18

Key Features

- **Excellent thermal insulation:** Resistant to contact heat up to 250°C
- **Good cut and abrasion resistance:** For durable hand protection gloves
- **Extended cuff:** Enhanced forearm protection, reduced injury risks

Performance Standards & Regulatory Compliance



EN388: 2016



224XB

EN 407



X2XXXX

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 97-335	Coating Material: N/A Liner Material: Polycotton, Jersey Cuff Style: Gauntlet	7	10	360mm	Not Applicable	6 pairs/bag, 8 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.