



AVCam 300

Digital Camera and Camcorder for ARCHOS VIDEO AV300 series

Features & Specifications

The world's first combined 3.3 Megapixel camera, MPEG4 camcorder, MP3 recorder and USB 2.0 hard disk is here. All integrated seamlessly with the VIDEO AV320 or 340 from ARCHOS.

The compact AVCam 300 is full of innovations that have been designed especially for use with the VIDEO AV300 series. A simple press-fit attaches the AVCam 300 onto your VIDEO AV320 or 340 allowing you to enjoy it's many fantastic features:

- Unique combination of MPEG4 camcorder and digital still camera: within seconds you can switch the functionality of the AVCam 300 from camcorder to still camera.
- 3.3 Megapixel (effective) CCD, matched optical system and advanced imaging technology for high resolution crystal clear pictures and video.
- 10x digital and 3x optical zoom Ricoh lens
- Massive storage: 40,000 3.3-Megapixel photos*
- Camcorder to record up to 80 hours of MPEG4 video, QVGA (320x240) 18f/s, with MP3 stereo sound.
- Stereo audio recording and real-time encoding directly into MP3.
- View your videos and photos instantly on the large 3,8" built-in color LCD or on larger screen size by connecting yc VIDEO AV300 series to any TV or monitor.
- Several program modes for automatic control of exposure, white balance and color saturation
- Ultra-fast USB 2.0 transfer of videos and photos to and from your computer. The VIDEO AV300 series contains a hard disk, that will be mounted as an additional hard disk when connected to a computer. This allows easy file management.



Explore this unique, innovative add-on for work and play.

Enrich your VIDEO AV300 experience by clicking other optional add-ons: Digital Video Recorder, Memory Card Reader and FM Radio & Remote Control.

* Depending on resolution chosen and on capacity of the Jukebox hard disk. Figures given 40GB hard disk.

MPEG-4 Camcorder:	MPEG4 SP, QVGA (320x240), 18 f/s, AVI file format, can be read by DivX™ and XviD viewers. MP3 stereo sound stream
Digital Still Camera:	3.3 Megapixel JPEG
Lens:	Ricoh 3x zoom lens 6.2-18.6mm
Adjustable resolutions:	2048x1536, 1600x1280, 1280x960, 1024x768, 800x600, 640x480, 320x240
Program modes:	Automatic exposure & white balance, daylight, overcast, tungsten and fluorescent. View MP4 videos and JPEG photos instantly on built-in-color LCD or TV.
Dimensions:	165x90x48mm (6.5"x3.5"x1.9") with AV320, 55x90x48mm (2.1"x3.5"x1.9") without
Weight:	450g (16 oz) with VIDEO AV, 150g (5.3 oz) without.
Package Includes:	AVCam 300, Carrying Pouch, 6-language Installation Sheet.

* DivX is an international trademark of DivXNetworks Inc.
