




3636 - FEMALE BULKHEAD CONNECTOR, BSP PARALLEL



maximum working pressure	30 bar 3 MPa 435 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	FDA CHEMICAL NICKEL PLATED BRASS
retaining nut	FDA CHEMICAL NICKEL PLATED BRASS
'O'-rings	FKM
collar	FDA CHEMICAL NICKEL PLATED BRASS
sealing washer	FDA CHEMICAL NICKEL PLATED BRASS

[inch Part numbers](#)
[Convert to inch](#)
[Convert to oz](#)
[Reset Filters](#)

Part Nb	ØD (MM)	C	E (mm)	(mm)	F2 (mm)	H (mm)	H1 (mm)	K (mm)	ØTmini (mm)	 (kg)
	All	All	All	All	All	All	All	All	All	All
3636 04 10	4	G1/8	8.5	14	14	30.5	11	15	13	.02
3636 06 10	6	G1/8	8.5	17	17	33	11	18.5	15	.033
3636 06 13	6	G1/4	11.5	17	17	37	15	18.5	15	.033
3636 08 10	8	G1/8	8.5	19	19	34	10.5	21	17	.044
3636 08 13	8	G1/4	11.5	19	19	38	14.5	21	17	.044
3636 10 17	10	G3/8	12	22	27	42.5	16	24	21	.073
3636 12 17	12	G3/8	12	24	24	43	16	26	23	.077
3636 12 21	12	G1/2	16	27	24	48.5	21.5	29.5	23	.133