



Datasheet

ENGLISH

RS PRO 10 Way Unscreened Flat Ribbon Cable

Stock No: 214-0677



Product Details:

Ribbon Cables 7/0.15 mm

An individually stranded ribbon cable.

Features and Benefits

- Colour-coded
- Individually stranded
- PVC insulated tinned copper conductors
- 10-way 12 x 1.3mm., 20 way 25 x 1.3mm

Standards: UL listed to UL1007

Specifications:

Number of Ways:	10
Pitch:	1.27mm
Reel Length:	25m
Width:	12.7 mm
Cable Shape:	Ribbon
Voltage Rating:	300 V
Screened/Unscreened:	Unscreened
Conductor Strand Type:	Stranded
Number of Strands:	7
Minimum Operating Temperature:	-20°C
Maximum Operating Temperature:	+80°C
Size of Strands:	0.15 mm
Capacitance:	50 pF/m
Characteristic Impedance:	100 Ω
Core Strands:	7/0.15 mm