

## Han 10HPR-Compact-CM-for CL



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 510 5481
Specification	Han 10HPR-Compact-CM-for CL
HARTING eCatalogue	<a href="https://harting.com/09405105481">https://harting.com/09405105481</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> HPR Compact
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings

### Version

Size	10 HPR
Locking type	Central locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP6K9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR



**Pushing Performance**  
Since 1945

## Material properties

Material (locking)	Stainless steel
--------------------	-----------------

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	130 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140901858
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467