## **Crocodile Clips**



### **Features**

- Uninsulated steel crocodile clip
- Silver in colour
- Spring-loaded
- Current rating of 25 A
- Jaw opening of 30 mm.
- Contacts made of steel with a nickel-plated finish to be durable for continuous use.
- The integral cable clamp has a secure 4mm screw fixing
- Able to accommodate a 4 mm banana plug.
- The enhanced finger grip on the handles ensures a simple operation.

# RS PRO Crocodile Clip Connection, Nickel-Plated Steel Contact, 25A, Silver

RS Stock No: 180-6618



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## **Crocodile Clips**



#### **Product Description**

This steel crocodile clip can be used to create temporary, flexible connections safely and is one of the simplest methods of linking up component's cables and wires in circuits.

The clip has large spring-loaded jaws which open to 30 mm in width, making it simple to attach to and detach from batteries or components. The enhanced finger grip on the handle makes this clip easy to use and once clamped in place allows the user to release the grip on the connector securing it in place.

At the opposite end of the clip there is a secure 4 mm screw fixing, enabling effortless connection to a range of common cables, devices, and equipment. With steel contacts that are resistant to oxidation and other types of corrosion, these contacts are nickel-plated to further improve durability. These crocodile clips are ideal for attaching onto wires or cables to create an electrical connector, the clip is attached to components and establishes a connection between the two.

### **General Specifications**

Current Rating	25A
Jaw Opening	30mm
Screw/Nut and Washer	M4 x 6mm
Rated Voltage	50 V
Contact Material	Nickel-Plated Steel
Insulated	No
Colour	Silver
Connector Type	Large Crocodile Clip

#### Dimensions

