

Angle Grinder LXT®

DGA463

18V • 115 mm • 3 000 – 8 500 min⁻¹

Powerful angle grinder

A 18V powerful cordless angle grinder. The Angle grinder can be connected to a dust extraction system with optional dust-collecting wheel cover. Anti-restart function.



LXT **BL** **ADT** **AFT** **BRAKE**

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	3000 - 8500 min ⁻¹
Spindle Thread	M14
Bore Size (Arbor Diameter)	22,23 mm
Disc Diameter	115 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
Vibration Level, Disc Sanding	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Disc Sanding	1,5 m/s ²
Vibration Level, Surface Grinding	6,5 m/s ²
Vibration Uncertainty (K Factor), Surface Grinding	1,5 m/s ²
Sound Power Level (L _{WA})	90 dB(A)

User benefits

- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Compact and lightweight design
- Electric brake for maximum productivity and increased operator safety
- Brushless motor eliminates carbon brushes, enabling the Brushless motor to run cooler and more efficiently for longer life
- 3-stage LED gauge indicates battery charge level / overheating / overload
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing