



PCB LAYOUT

SPECIFICATIONS:

MATERIAL:-

MOULDING: NYLON 9T, UL94V-0

CONTACT: PHOSPHOR BRONZE, T=0.2MM

FINISH:-

TIN (SEMI GLOSS)

ELECTRICAL:-

CURRENT RATING: 1A AC/DC

WORKING VOLTAGE: 50V AC/DC

WITHSTANDING VOLTAGE: 500V AC/MINUTE

CONTACT RESISTANCE: 30 mΩ MAX.

INSULATION RESISTANCE: 100 MΩ MIN.

ENVIRONMENTAL:-

TEMPERATURE RANGE: -25°C TO +85°C

NOTES: ALL DIMENSIONS AND NOTES

MARKED ✕ ARE CRITICAL AND

MUST BE CHECKED IN ACCORDANCE

WITH QUALITY DOC. QI-02A

NO. OF WAYS	PART NO	DIM (MM)	
		A	B
2	M40-4010246R	1.00	4.00
3	M40-4010346R	2.00	5.00
4	M40-4010446R	3.00	6.00
5	M40-4010546R	4.00	7.00
6	M40-4010646R	5.00	8.00
7	M40-4010746R	6.00	9.00
8	M40-4010846R	7.00	10.00
9	M40-4010946R	8.00	11.00
10	M40-4011046R	9.00	12.00
11	M40-4011146R	10.00	13.00

NO. OF WAYS	PART NO	DIM (MM)	
		A	B
12	M40-4011246R	11.00	14.00
13	M40-4011346R	12.00	15.00
14	M40-4011446R	13.00	16.00
15	M40-4011546R	14.00	17.00
16	M40-4011646R	15.00	18.00
17	M40-4011746R	16.00	19.00
18	M40-4011846R	17.00	20.00
19	M40-4011946R	18.00	21.00
20	M40-4012046R	19.00	22.00

④

*NOTE:

REMOVE R FOR LOOSE BAG PACKING

ORDER CODE

M40-401 XX 46R

NO. OF WAYS — WITH R: REEL PACKING

⑤ WITHOUT R: LOOSE PACKING
(10pcs PER STRIP, 10 STRIPS PER BAG)

Allan	5	25.09.08	A164
Allan	4	27.06.08	A136
Allan	3	19.06.08	A130
Allan	2	08.03.07	A022
Allan	1	01.08.06	-

NAME	ISS.	DATE	C/NOTE

APPROVED: *Paul*CHECKED: *Paul*

DRAWN: Allan

CUSTOMER REF.:

ASSEMBLY DRG:

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.15mm
X.XXX = ±0.08mm
ANGLES = ±5°
UNLESS STATED

MATERIAL: SEE NOTES
FINISH: SEE NOTES
S/AREA: mm²

TITLE: WAFER 1.00MM SIDE ENTRY SMT TYPE

DRAWING NUMBER: M40-401 XX 46R

SHT
1
OF
1