

2U 19in Steel Vertical Wall Mount Equipment Rack Bracket

Product ID: RK219WALLV



The RK219WALLV 2U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution allowing rackmount equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 2U bracket can be installed horizontally under a desk, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Perfect for SoHo (small office, home office) environments, the wallmount bracket features a sturdy steel design constructed to EIA-310 19in rack standards, and offers space-savings for environments lacking the footprint space for a full size server equipment rack. Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes are positioned at exactly 16in apart, matching standard construction framework.

Backed by a StarTech.com Lifetime Warranty.

Need more storage space? StarTech.com also offers a [3U 19in Wallmount Bracket](#) and a [4U 19in Wallmount Bracket](#).

Certifications, Reports and Compatibility



Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

Features

- Constructed to meet EIA-310 19" rack standards
- Made from solid steel for durability
- TAA compliant for GSA Schedule purchases
- Compatible with most 19" rack mountable equipment
- Arrives fully assembled with cage screws and nuts for mounting equipment
- Wall mounting holes are 16" center to center for greater stability, and mounting into standard wall studs
- Equipment can be vertically wall mounted, or horizontally under a desk

Hardware	Warranty	Lifetime
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	2-Post
	U Height	2U
	Wallmountable	Yes
Performance	Weight Capacity	125.3 lb [56.7 kg]
Special Notes / Requirements	Note	Package includes 1 ½" screws for mounting to wood surfaces, additional hardware will be required for other materials
Physical Characteristics	Color	Black
	Construction Material	Steel
	Enclosure Type	Steel
Product Measurements	Product Height	4.1 in [10.5 cm]
	Product Length	5.9 in [15.1 cm]
	Product Width	19.8 in [50.4 cm]
	Weight of Product	26.4 oz [748.7 g]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	4.6 in [11.6 cm]
	Package Length	21 in [53.3 cm]
	Package Width	6.6 in [16.8 cm]
	Shipping (Package) Weight	2.7 lb [1.2 kg]
What's in the Box	Included in Package	1 - Vertical Wall Mount Bracket
		8 - M5 Cage Nuts
		8 - M5 Screws
		6 - Wood Screws
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.