



Bubblemat Connect

Interlocking tile version of our popular bubble surface mat

- Three modules can be linked together to cover any shaped area.
- Raised bubbled surface to stimulate blood circulation.
- Soft but sturdy rubber material offers comfort from cold hard concrete floors.

Technical Specification

Material:	Natural rubber
Surface Finish:	Bubble shaped
Product Height:	14mm
Operating Temperature:	-30°C to +50°
Resistance to Chemicals:	Resistant to water and most mild acids
Environmental Resistance:	Use predominantly in dry areas
Cleaning Method:	Use a high pressure hose (not exceeding 60psi) to remove the dirt and debris on the mats. For best results use a mild detergent (pH 4.0-9.0) to clean the mats. Do not use steam or degreasers or caustic chemicals. Do not mechanically scrub the mats
Country of Origin:	Sri Lanka

Sizes	Black	Safety	Weight
50cm x 50cm (Middle)	BF010007	-	11.00 kg
50cm x 50cm (End)	BF010008	BF010708	11.00 kg
50cm x 50cm (Corner)	BF010009	BF010709	11.00 kg

