


## GigaDuct Elbow, Vertical Down, 90°, 50mm, with Cover

Art.-Nr. 181-00390 | LG-BVOD90-YL 



- 50mm wide
- 90° Bend
- Supplied with cover
- For creating vertical downward routing transitions from horizontal routes
- Fully encloses cables to keep out dirt and dust as the fibre is routed through different areas of the data centre
- Protects cables by maintaining proper bend radius, preventing micro bends and macro bends that degrade performance
- it



More products in this product group:

[Fittings >](#)



Application	vertical outside elbows are used for creating a vertical downward transition from GigaDuct horizontal routes. This model offers a 90° bend and is supplied with cover.
Colour	Yellow (YE)
PART DESCRIPTION	LG-BVOD90-YL
Product Family	Elbow - Vertical Outside
Product Group	Fittings
Short Description	GigaDuct Elbow, Vertical Down, 90°, 50mm, with Cover
Technical Description	GigaDuct is a robust, scalable cable management system engineered specifically for organising and protecting optical fibre cables in the data centre environment. Constructed with precision, it provides a dedicated pathway that prevents cable congestion, minimises physical stress on fibres, and facilitates efficient cable management. Whether you are setting up a new data centre or upgrading an existing one, HellermannTyton's GigaDuct offers unmatched versatility and reliability.
Type	LG-BVOD90-YL

## Product Dimensions

Angle	90
Height (H)	140 mm
Length (L)	140 mm
Width (W)	76 mm

## Specifications

Halogen-free	Yes
Limited Fire Hazard	Yes
ROHS compliant	Yes

Specifications



## Logistics and Packaging

Country of Origin	GB
Dimensions W x H x D	76 mm x 140 mm x
GTIN-13 / EAN	4031026495477

## More Information

