



Features

-



Product Overview

Product name	SYLPIPE L1200 2020LM 3CCT IP20
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
General application	Residential & Consumer, Retail
ETIM Class	EC000109
Fixture luminous flux (lm)	2020
Luminaire efficacy (lm/W)	138
Correlated colour temperature (k)	4000
Light colour	Warm White or Neutral White or Daylight
CRI (Ra)	80
Photobiological Risk Group	RG1
Total power consumption (W)	15
Electrical protection	Class II
Dimmable	No
IP rating	IP20
IK rating	IK03
Product EAN number	5410288902432
Warranty	3 years
Dimming method	N/A



SYLPIPE L1200 2020LM 3CCT IP20
0090243

Data table

GENERAL DATA

Product name	SYLPIPE L1200 2020LM 3CCT IP20
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
General application	Residential & Consumer, Retail
ETIM Class	EC000109
Warranty	3 years

OPTICAL DATA

Fixture luminous flux (lm)	2020
Luminaire efficacy (lm/W)	138
Correlated colour temperature (k)	4000
Light colour	Warm White or Neutral White or Daylight
CRI (Ra)	80
Photobiological Risk Group	RG1

ELECTRICAL DATA

Total power consumption (W)	15
Primary Supply/Product voltage - min (V)	220.0
Primary Supply/Product voltage - max (V)	240.0
Lamp power factor	0.5
Electrical protection	Class II
Control gear required	No
Dimmable	No
Dimming method	N/A
Inrush Current (A)	10.5
Inrush Duration (µs)	144
Energy Efficiency Class (A->G) of contained light source	D
Nominal Frequency (Hz)	50/60Hz

SYLPIPE L1200 2020LM 3CCT IP20 0090243

Connectable conductor cross section - Max (mm ²)	0.75
---	------

LIFETIME DATA

Lifespan L70 B50	30000
------------------	-------

PHYSICAL DATA

IP rating	IP20
-----------	------

IK rating	IK03
-----------	------

Nominal Product Length (mm)	1194
-----------------------------	------

Nominal Product Width (mm)	24
----------------------------	----

Nominal Product Height (mm)	35
-----------------------------	----

Weight (kg)	0.177
-------------	-------

PACKAGING

Product EAN number	5410288902432
--------------------	---------------

Packaging single length / height (cm)	138.0
---------------------------------------	-------

Packaging single width (cm)	4.0
-----------------------------	-----

Packaging single depth (cm)	3.2
-----------------------------	-----

DUN14 (inner)	15410288902439
---------------	----------------

Units per outer package	24
-------------------------	----

Packaging outer length / height (cm)	139.5
--------------------------------------	-------

Packaging outer width (cm)	18.5
----------------------------	------

Packaging outer depth (cm)	22.5
----------------------------	------

SAFETY DATA

Special purpose lamp	No
----------------------	----

Dry applications use only	No
---------------------------	----

Suitable for household illumination	No
-------------------------------------	----