

**The Luxury**  
**Koolbreeze Climateasy 14**  
**14000btu**  
**Portable Air Conditioner**

**Instant cooling and heating**



**14000btu of Luxury**

We present the **Koolbreeze Climateasy 14**; the portable air conditioner designed for those larger rooms and offices where you require cooling or heating all year round. It can make your lounge or office cool and comfortable and thanks to its ultra – quiet operation, it won't disturb your train of thought.

This Portable Air Conditioner packs 14000btu of cooling (and heating) power. This model is an air conditioner, heater, dehumidifier and fan. It is an energy efficient multi-season unit utilizing heat pump technology to extract heat from the air while consuming less energy than other portable units and thus has an "A" grade efficiency rating

Our evaporative technology uses any collected moisture to cool the unit before it is eliminated through the exhaust ducts leaving no water bucket to empty.

**Multi-season air conditioner and heater in one  
super compact unit**

**SPECIFICATION (please compare with rival products)**

- 14000 BTU (4.1 Kw) Heating & Cooling
- 24-hour programmable on and off timer
- 36 Litre per day evaporative dehumidifier
- Adjustable thermostat down to 16°C
- 3 speed fan with oscillating louvers
- Easy rolling casters for portability
- Cooling input 1.45kW
- Heating input 1.50kW
- Air Circulation 450m³/h
- Noise ; Less than 50 db(A) sound pressure
- Size 410x440x830mm
- Weight 32Kg net/ 34Kg gross
- Extra long hose 2M x 147mm
- For use between 7C and 35C
- **Energy Efficiency Rating A**



**Window Kit  
Included**

**Includes  
Remote control unit**

Unit must be vented outside when in AC and heater modes.  
For the purposes of EU regulation EN12102 this is a "local air conditioner" and produces less than 65DbL sound energy.