



Government Solutions

Market

- + Defense
 - Energy
 - Green Solutions
 - Health Safety
 - Homeland Security

Contracts

- General Services Administration
- Veterans Affairs

Product Information

- Government Catalogs
- Online Product Catalog
- FEDSPEC Locator
- NSN Locator

News

- Industry Links

Contact Information

- Contact Us

[Product Catalog for Government Solutions](#) > [Defense Solutions](#) > [Ships/Fleet Maintenance Products](#) > [3M™ Component Handling Solutions](#) > [3M™ Tapes](#) > [3M™ Anti-Static Tapes](#) > [3M™ Anti-Static Utility Tape](#) >

3M™ Antistatic Utility Tape, 40PR, 5/8 in x 72 yd (22.23 mm x 66 m)



2.2 mil Printed Polyester Film

[Click to Enlarge](#)

Where To Buy

[Where to Buy](#)

Quick Links

- [Contact Us](#)
- [Material Safety Data Sheets \(MSDS\)](#)
- [OH&ES Distributor Login](#)
- [Industrial Distributor Login](#)

[Additional Information](#) [Documents](#) [Packaging](#)

3M Antistatic Utility Tape 40 combines 3M’s remarkable antistatic adhesive with a clear, one mil polyester film backing, and is perfect for use in static-sensitive areas. An optional special pattern of ESD symbols alerts users that this is the only tape that should be used in static-safe areas.

At the heart of all 3M antistatic tapes is a unique conductive polymer adhesive that suppresses static, both during unwind from the roll and during removal from a surface. They generate less than 50 volts on unwind from the roll or removal from a stainless steel surface, even in extremely dry conditions of 10% relative humidity.

Use Antistatic Utility Tape 40 as a third hand to hold work orders, notes, documentation, or instructions in place; to seal static shielding bags and boxes containing electronic components; or to bundle DIP tubes and JEDEC shipping trays. It can also be used to hold down obstructions such as wires or attachments during manufacturing.

3M ID: 80-1006-1161-7

GTIN(UPC/EAN): 0 00 51138 51489 1

Characteristics:

Name	Value
Adhesive Type	Conductive Polymer
China RoHS - Below MCV	Yes
EU RoHS Compliant	Yes
Material	Polvester

Part Number	1087, 8888
Size	0.625 in x 72 yd. (15.8 mm x 66 m)
Tape Length	72 yd (66 m)
Tape Thickness	2.2 Milli-inch (mil)
Tape Type	Anti-Static Utility
Tape Width	0.625 in (1.5 cm)
Thickness	2.2 Millimetre

