

MFS SERIES - MICRONIC FILTER

MFS - Replacement cartridge for MFS regular - Coalescing filter
: 0,01 µm



Part number	Flow rate at 7 bar (m3/h) (ΔP= 0,10 bar)	Temperature min/max (°C)	Max. operating pressure (bar)	Filtration (µm)
MFSC 5532	55	3 / 80	20	0,01
MFSC 7040	70	3 / 80	20	0,01
MFSC 10060	100	3 / 80	20	0,01
MFSC 15090	150	3 / 80	20	0,01
MFSC 225130	225	3 / 80	20	0,01
MFSC 300175	300	3 / 80	20	0,01
MFSC 400235	400	3 / 80	20	0,01
MFSC 500295	500	3 / 80	20	0,01
MFSC 800470	800	3 / 80	20	0,01
MFSC 1550910	1.550	3 / 80	20	0,01