

manifold block

VABM-B10-25S-G38-7

Part number: 8026266

FESTO



Data sheet

Feature	Value
Grid dimension	27.5 mm
Assembly position	Any
Max. number of valve positions	7
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Product weight	1,143 g
Mounting type	with through hole
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 3	G3/8
Pneumatic connection, port 5	G3/8
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminium alloy