



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2020-03-16	Allen Pan	Rev.02 To Rev.A



AB-AU08ML-UPBML-QHXXX  
 XXX: 0.5~99Meters  
 A05: 0.5Meter  
 001: 01Meter  
 002: 02Meters  
 :  
 :  
 099: 99Meters

- Note:
- \*  $\varnothing$  Important Dimension To Check.
  - \* C1  
 Waterproof Rate: IP68, Mated.  
 Housing: Thermoplastic, Black.  
 Pin: Copper Alloy, Gold Plated.
  - \* C2  
 Plug: RJ45 Plug, 8P8C.
  - \* Cable: CAT-5E, UTP, 24#\*4P.  
 PVC Jacket, OD=6mm, Black.
  - \* Cable Length Tolerance:  
 $\leq 0.3M$ : +25/-0mm.  
 $> 0.3M \sim 1.5M$ : +60/-0mm.  
 $> 1.5M \sim 3M$ : +120/-0mm.  
 $> 3M \sim 5M$ : +160/-0mm.  
 $> 5M \sim 10M$ :  $\pm 100mm$ .  
 $> 10M \sim 20M$ :  $\pm 200mm$ .  
 $> 20M \sim 30M$ :  $\pm 300mm$ .  
 $> 30M \sim 100M$ :  $\pm 500mm$ .



8	Brown	棕	8	Twist 對線
7	White/Brown	白/棕	7	
6	Green	綠	6	
5	White/Blue	白/藍	5	Twist 對線
4	Blue	藍	4	
3	White/Green	白/綠	3	Twist 對線
2	Orange	橙	2	
1	White/Orange	白/橙	1	
C1	Wire Color		C2	

UNIT: mm	TOLERANCE	TITLE	DWG NO	CUSTOMER	DRAWN BY	DATE
$\pm 0.5$ mm	$\pm 0.5$ mm	XLOK, A-2A, DOUBLE-ENDED, M, 08P	AB-AU08ML-UPBML-QHXXX	ALTW	Allen Pan	2020-03-16
SCALE: Free	SHEET: 1 OF 1				Checked BY: Sam Ho	DATE: 2020-03-16
REV: A	SIZE: A4	©: Inspection Item			APPROVED BY: Fred Lee	DATE: 2020-03-16

**Amphenol LTW**  
 安費諾亮泰企業股份有限公司