

Bellows kit EADB-V2-50-S10-100

Part number: 2828839

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Outside diameter	93 mm
Size	50
Stroke range	10 mm ... 100 mm
Piston rod extension	46 mm
Design	Round
Mounting position	optional
Design	Bellows kit With ducted exhaust air
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media resistance	Dust Chips Oils Grease Petrol
Degree of protection	IP65 To IEC 60529
Ambient temperature	-10 °C ... 80 °C
Moving mass	93 g
Product weight	190 g
Type of mounting	Push-on Via threaded pin
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material adapter components	Wrought aluminium alloy Anodised
Material seals	NBR
Material bellows	NBR
Material threaded pin	High-alloy stainless steel